Signomat S200



Electro-Chemical Marking "Made in Germany

- * Electrolytic marking of metal items of different shapes and sizes with: letters and numbers, graphics, trade marks, scales, data and logos.
- * Choice of light / dark markings, exact adjustment of the marking time.
- * Suitable for small and mid-size series.
- * End of marking time is indicated by an optical and acoustic signal.
- * Versatile, sturdy and durable.



A class better!

It's so simple and quick: Electrolytic marking on flat. convex. concave or round surfaces.





- * Controlled by micro-processor
- * Illuminated, digital display of all parameters
- * Electronic short-circuit protection

Accessories For optimum results

Accessory set



Marking felt



To cut your own sizes 375 x 500 mm Art.-No.: 22.150

Stencils



All phototechnical possibilities

Stamps



Shapes for almost all part geometries

Electrolyte



Application specific Electrolytes Art.-No.: 22.001

Art.-No.: 22.040

Edition: 01/11

Neutralyte



With pH indicator Art.-No.: 22.102

Neutralyte dispenser



For fast, economic and clean after-treatment Art.-No.: 22.156

K:\Prospekte\Signiertechnik\Prospekt-Erstellung\S200_GB.cdr

Schilling Marking Systems GmbH In Grubenäcker 1 DE - 78532 Tuttlingen



+49 (0)7461 9472-0



+49 (0)7461 9472-20



Signomat S200



Optional Accessories



Art.-No.: 56.072

Workholding unit for small series

- * Exact alignment of the parts to the stencil
- * For small series
- * Accurate adjustment of the stencil
- * Fast replacement of the jigs



Art.-No.: 56.073

Etch-Station M1 with Electrolyte supply

- * With automatic supply of Electrolyte
- * For small and mid-size series
- * Exact alignment of the workpiece to the stencil
- * Accurate adjustment of the stencil
- * Fast replacement of the jigs

SIGNOMAT S200 - Technical Specifications


Dimensions W,H,D: 265, 95, 275 mm

Mains voltage: 115/230 V 50/60 Hz (automatic recognition)

Marking voltage: 12 V Marking current: 3,3 A Current types: Light/Dark Output: 40 VA Weight: 4 kg Noise level:

Operation modes: - manual stamp with automatic start-up

- manual marking together with a foot switch



K:\Prospekte\Signiertechnik\Prospekt-Erstellung\S200_GB.cdr









Edition: 01/11